



12S (with Cleaver for scale)



Workstation in Transit Case



Workstation on Transit Case



Fujikura 12S Kit 1

Fujikura 12S Fusion Splicer

The Fujikura 12S is the world's smallest, lightest and most portable fusion splicer available today. Despite its incredibly small size, this ruggedized, full-featured unit offers unmatched versatility for splicing in the most challenging environments. The innovative transit case and work tray provide multiple options for the best utilization of available work space while the long life battery provides power for up to 100 splice cycles which include application of the splice protection sleeve.

The Fujikura 12S incorporates features typically found only in more expensive models. The large 4.5" monitor provides a crystal clear image, even in the brightest sunlight, for evaluating splice quality. The electrode life has been extended to 3,000 splices, minimizing downtime for replacement and stabilization. Software updates are accomplished via the internet allowing users to quickly update their software as new splice programs become available. The fully ruggedized chassis provides for shock, dust and moisture protection while the two camera observation system provides for accurate fiber alignment and loss estimation calculations. The Fujikura 12S is also fully compatible with the FuseConnect line of fusion installable connectors.

Backed by the best service team in the industry, the Fujikura 12S is the ideal splicer to use when portability, ruggedness, versatility and reliability are needed for your splicing application.

Features

- World's smallest splicer at 4.76"W x 6.38"D x 2.24"H
- Fully ruggedized for shock, moisture and dust resistance
- Transit case converts to easy to use workstation
- Dual camera, fixed v-groove alignment technology
- Extended life electrodes
- Long life battery (100 splices/shrinks per charge)

Ordering Information

DESCRIPTION	AFL NO.
Fujikura 12S Fusion Splicer Includes: Fujikura 12S Fusion Splicer, ADC-19 AC Adapter, BTR-10 Battery Pack (installed), FH-60-250 Fiber Holders (Pair), ACC-09 Power Cord, ELCT2-12 Spare Electrodes (Pair), Operation Manual on CD, Quick Reference Guide, AP-01 Alcohol Container, SD01 Screwdriver and CC-29 Transit Case	S015521
Fujikura 12S Fusion Splicer Kit 1 Includes: Fujikura 12S Fusion Splicer, CT-30 Cleaver, ADC-19 AC Adapter, BTR-10 Battery Pack (installed), FH-60-250 Fiber Holders (Pair), FH-60-900 Fiber Holders (Pair), ACC-09 Power Cord, ELCT2-12 Spare Electrodes (Pair), Operation Manual on CD, Quick Reference Guide, AP-01 Alcohol Container, SD01 Screwdriver and CC-29 Transit Case	S015522
Fujikura 12S Fusion Splicer Kit 2 Includes: Fujikura 12S Fusion Splicer, CT-10 Cleaver, ADC-19 AC Adapter, BTR-10 Battery Pack (installed), FH-60-250 Fiber Holders (Pair), FH-60-900 Fiber Holders (Pair), ACC-09 Power Cord, ELCT2-12 Spare Electrodes (Pair), Operation Manual on CD, Quick Reference Guide, AP-01 Alcohol Container, SD01 Screwdriver and CC-29 Transit Case	S015530

Fujikura 12S Fusion Splicer

Accessories & Supplies

DESCRIPTION	AFL NO.
Cleavers	
CT-10 Cleaver (for single fibers)	S015533
CT-30 Cleaver (for single to 12 ribbon fibers)	S014076
Fiber Holders	
FH-60-250 (250 μm single fiber)	S014548
FH-60-900 Fiber Holders (900 μm single fiber)	S014549
FH-60-DC250 (250 μm drop cable)	S015528
FH-FC-20 (900 μm within 2.0mm sheathing)	S014696
FH-FC-30 (900 μm within 3.0mm sheathing)	S014695
FH-60-LT900 (900 μm loose buffer tube)	S015181
Batteries	
BTR-10 Battery Pack	S015527
Miscellaneous	
ELCT2-12 Electrodes	S014052
ADC-19 AC Adapter	S015523
ACC-09 Power Cord	S014390
AP-01 Alcohol Container	S015525
SD-01 Screwdriver	S015526
CC-29 Transit Case	S015524

Specifications

PARAMETER	VALUE
Model	Fujikura 12S Fusion Splicer
Applicable Fibers	Single-mode (G.652 & G.657), Multimode (G.651), DSF (G.653), NZDS (G.655)
Number of Fibers	Single fiber
Cladding Diameter/Coating Diameter	125 μm / 160 μm to 3 mm by fiber holder system
Cleave Length	5 mm to 13 mm
Splice Mode / Heating Mode	Total 100 splice modes / 30 heating modes
Typical Average Splice Loss	0.05 dB (SM), 0.02 dB (MM), 0.08 dB (DS) and 0.08 dB (NZDS)
Splice Time/Tube Heating Time	Typical 15 sec with SM / Typical 30 sec with FP-03 (60 mm) sleeve
Splice Result Storage	Last 2,000 splices
Viewing Method/Magnification	2 axis CMOS camera with 4.47 inch color LCD/100X magnification
Tension Test	1.96 to 2.25 N
Number of Splice/Heat with Battery	Typical 100 cycles with BTR-10
Electrode Life	3,000 splices
Operating Condition	Altitude: 0 to 3,660 m above sea level, Wind: 15 m/sec Temperature: -10 to 50 deg C, Humidity: 0 to 95% RH, non-dew
Rugged Features	Shock resistance: 76 cm (30 inch) bottom surface drop Dust resistance: Exposure to dust (0.1 to 500 μm dia. Alumina Silicate) Rain resistance: H=10 mm/hr for 10 min
Dimensions	121W x 162D x 57H (mm) / 4.76 W x 6.38 D x 2.24 H (inches)
Weight with Battery	776 g / 1.71 lbs.